

1/2"OCML CCD

ICD-47/47E

Low Light High IR Sensitivity B/W CCD Camera



ICD-47(EIA)/47E(CCIR) is a high-sensitivity, higher-resolution B/W surveillance camera with 1/2"CCD for high-quality pictures. The camera incorporates Line-Lock, Auto Shutter, Back-light compensation, two way Auto Iris and delivers horizontal resolution of 570TV lines(EIA)/560TV lines(CCIR) with Minimum Illumination of 0.02 Ix/f1.4. Smear Level -120dB. The camera also supports near infrared imaging.

- ■Horizontal resolution 570 TV Lines(EIA), 560TV Lines(CC1R)
- ■Minimum illumination 0.02 Ix/f 1.4, 0.0065 lx/f0.8 equivalent.
- ■infrared sensitivity Five Times higher than conventional cameras with IT-CCD.
- ■Smear level -120dB high-quality picture, provides crisp pictures.

- Auto shutter function and low smear feature permits high light video level.
- Back Light Compensation(BLC)
- Video iris lens or DC iris lens can be used.
- Switchable Line-Lock/Internal Lock.
- ■Flange back adjustable.

ICD-47[EIA]/47E[CCIR]

1/2"OCML CCD Low Light High IR Sensitivity B/W CCD Camera

Specifications

Pickup Device 1/2" Interline Transfer CCD

Picture Element EIA:768(H)×494(V), approx. 380,000 pixels CCIR:752(H)×582(V), approx. 440,000 pixels

Image Size 6.4mm(H)×4.8mm(V)

Scanning System EIA:525 TV Lines/60Hz, 2:1 Interlaced CCIR:625 TV Lines/50Hz, 2:1 Interlaced

Sync System EIA:H 15.734kHz/15.75kHz, V 59.94Hz/60Hz

CCIR:H 15.625kHz, V 50Hz

GENLOCK Input VBS or VS 1.0Vp-p/ 75Ω (High impedance) (OPTION) BBS 0.45p-p/ 75Ω (High impedance)

S/N Ratio 46dB or more (AGC OFF, Detail OFF, Weight ON)

Minimum Illumination 0.02 k/f1.4 (AGC ON)
AGC ON/OFF Switchable
approx. 0.45(Fixed)

Back Light Compensation ON/OFF Switchable, Level Adjustable

AES ON/OFF Switchable

Auto Iris Function Video Iris/DC Iris(Switchable and iris level adjustable)

Power Requirement AC24V \pm 10% 60Hz (EIA) AC24V \pm 10% 50Hz (CCIR)

AC24V \pm 10% 50Hz (CCIR) AC230V \pm 15% 50Hz (CCIR) DC12V (10.5V \sim 16V) (CCIR)

Power Consumption Less than 5W

 Dimensions
 W70×H60×D125mm(W2.76×H2.36×D4.92inch)

 Weight
 AC24:approx.720g(1.59lbs.)

AC230V:approx.960g(2.12lbs.) DC12V:approx.540g(1.19lbs.)

Ambient Temperature $-10^{\circ}\text{C} \sim +50^{\circ}\text{C}(13.5^{\circ}\text{F} \sim 122^{\circ}\text{F})$ Lens Mount CS Mount (C mount adapter can be used)

Input/Output Connector Video Output:BNC

Auto Iris Out put 4P Square type(D4-151N-100 or

equivalent)

AC24V/DC12V Input:2P Push in terminal

Operational Switches Sync.: INT/LL Switchable

Line Lock Phase Adjustment AES:ON/OFF Switchable

Back Light Compensation: ON/OFF Switchable, Level

Adjustable

AGC:ON/OFF Switchable Auto Iris:DC/Video Switchable DC Iris Level Adjustable


Accessories Operation Manual

C-Mount adapter
Auto Iris Connector

(E4-191J-100 or equivalent)

Dimensions

Unit: mm (inch)





Underwriters Laboratories Inc.

U21A997-SI-F1 Printed in Japan

Design and specifications are subject to change without notice.

Ikegami IKEGAMI ELECTRONICS (U.S.A.). INC.

■URL http://www.ikegami.com

HEADQUARTERS 37 BROOK AVENUE, MAYWOOD, NJ 07607 Phone: (201) 368-9171 Fax: (201) 569-1626

WEST COAST OFFICE 20603 EARL STREET, TORRANCE, CA 90503 Phone: (310) 370-2400 Fax: (310) 370-7131

SOUTHWEST OFFICE TWO DALLAS COMMUNICATIONS COMPLEX, 6309 NORTH O' CONNOR ROAD, SUITE 117,

IRVING, TX 75039-3510 Phone: (972) 869-2363 Fax: (972) 556-1057

Certified JQA-0755



MIDWEST OFFICE 747 CHURCH ROAD, UNIT C4 ELMHURST, IL 60126 Phone: (630) 834-9774 Fax: (630) 834-8689

SOUTHEAST OFFICE 5200 N.W. 33RD AVENUE, SUITE 111 FORT LAUDERDALE, FL 33309 Phone: (954) 735-2203 Fax: (954) 735-2227

Safety agency approval

ISO 9001